

FA Series Forward-Acting Rupture Disk System



A revolutionary pre-torque holder design that meets all of your rupture disk needs...

Bulletin no. 485000 © 2012 ZOOK Enterprises, LLC, all rights reserved Printed in U.S.A. 12-12-3M-CGG



High Performance Forward-Acting Rupture Disks and Holder

In a continued effort to provide cutting edge products and technologies for rupture disk users, ZOOK is pleased to introduce our FA Series of Rupture Disks and Holders. The FA Series offers one unique holder design for use with multiple types of ZOOK *Forward-Acting* metal rupture disks.

Features / Benefits

- Pre-Torque Design
 - ...pre-assembly of a rupture disk into a holder prior to field installation
 - ...removal of the assembly from the piping system for inspection without disturbing the seal integrity of the Rupture Disk ...pre-torque bolts properly seat the disk by engaging the holder bite
- One holder design
 - ...accepts multiple disk designs
- Disk dome is contained within the holder assembly
 - ...prevents damaging the disk during installation into mating flanges
- Locating pin
 - ...allows only forward-acting type disks to be mounted into holder
- Fluoropolymer coated socket head cap screws
 - ...resists corroding to holder assembly ...provides easy removal without special sockets


Polyethylene cap screw covers

...prevents debris from building up in cap screw head

• Sizes 1" thru 12"

 Standard Holder Materials: Carbon Steel, 316SS, Hastelloy®

 Holder information is permanently affixed to the O.D. of holder





• Bubble tight metal-to-metal bite and disk seal


FLOW DIRECTION

- Flow direction arrows on disk tag and holder
 - ...provide permanent visual verification that holder assembly is properly oriented in the piping system
- Flange class and type specific
 - ... guards against installing an assembly into mating flanges with a different pressure rating than the rupture disk holder
- Positioning hole in mounting lug
 - ...located in the exact position as the mating flange
 - ...allows for proper alignment
 - ...can be used as an extra "hand" when installing into horizontal piping









Safety Relief Valve Protection

When disk is mounted under a Relief Valve, the working components of the valve are isolated from hostile environments.

Option Liners

Teflon liners are available to provide protection from corrosive media. *Note that the maximum temperature ratings for disks supplied with liners is lower than the unlined disk.*

FAC Rupture Disk Features

- Designed for Non-fragmentation
- Standard operating ratio of 80% of the marked rating on disk tag-may be extended to 85% of the minimum burst pressure¹
- Excels in liquid, gas, or two-phase applications
- Standard manufacturing ranges of 0%, -5%, and -10% ensures marked rating on disk tag does not exceed the MAWP of equipment
- FAC-V designed to withstands full vacuum
- Unique design ensures proper disk orientation into holder
- 3-dimensional stainless steel tag is standard
- CE, and TUV compliance available (contact ZOOK for ASME UD marking)

Certified Flow Resistance factors (K_r)

Disk Type	K _{rl} (Liquid)	K _{rg} (Gas)		
FAC-R	TBD	TBD		
FAC-V	TBD	TBD		
FAX	TBD	0.39		


FAX Rupture Disk Features

- Designed for Non-fragmentation
- Standard operating ratio of 85% of the marked rating on disk tag-may be extended to 90% of the minimum burst pressure¹
- Excels in liquid, gas, or two-phase applications
- Standard manufacturing ranges of 0%, -5%, and -10% ensures marked rating on disk tag does not exceed the MAWP of equipment
- Minimum published pressures withstand full vacuum without vacuum support
- Resists product build-up. The smooth concave side of the disk is exposed to the process media
- Unique design ensures proper disk orientation into holder
- 3-dimensional stainless steel tag is standard
- ASME UD (gas service only), CE, and TUV compliance available

Holder Dimensions/Specifications

	Available ANSI Flange Class*	Minimum Height (in)*	Standard Height (in)						
Nominal Size			Short Pattern FAH	Mid Pattern FAH-LP1	Long Pattern FAH-LP2	Weight (Lbs.) (Short Pattern)	Number of Cap Screws	Cap Screws Hex Size	Gauge tap (NPT)**
1"	150/300/600	1-9/16"	2-1/8"	2-11/32"	2-9/16"	3.8	4	3/16"	1/8", 1/4"
1-1/2"	150/300/600	1-11/16"	2-1/4"	2-29/32"	3-9/16"	6.4	4	1/4"	1/8", 1/4"
2"	150/300/600	2-5/32"	2-23/32"	3-15/16"	5-5/32"	9.0	4	5/16"	1/8", 1/4"
3"	150/300/600	2-9/16"	3-1/8"	4-15/16"	6-23/32"	16.6	4	3/8"	1/8", 1/4"
4"	150/300	2-19/32"	3-5/32"	5-31/32"	8-3/4"	22.5	4	3/8"	1/8", 1/4"
6"	150/300	3-7/32"	3-7/16"	6-25/32"	10-3/32"	36.0	8	5/16"	1/8", 1/4"
8"	150/300	4-1/16"	4-5/8"	9-1/32"	13-15/32"	53.4	8	3/8"	1/8", 1/4"
10"	150	4-3/4"	5-21/32"	11-5/32"	16-11/16"	99.8	12	3/8"	1/8", 1/4"
12"	150/300	5-1/16"	6-17/32"	13-5/32"	19-25/32"	136.0	12	1/4"	1/8", 1/4"

^{*} Holders are also available to fit DIN and JIS flanging. Contact ZOOK for details.



^{*}Minimum height specified in table above will maintain the pre-torque feature of the rupture disk holder Refer to ASME/ANSI B16.5 Pipe flanges and Flange Fittings (Table 2) for Max allowable Pressure/Temperature Ratings per flange Class

Options/Accessories

Mid/Long Pattern

- Can be machined to meet existing piping specifications
- Prevents Rupture Disk membrane from protruding beyond the outlet holder after burst



Replacement Fluoropolymer Coated Cap Screws

Cap Screw Spections+				
Туре	Socket Head			
Material	Alloy Steel			
Hardness	38-43-RC			
Threads	UNRF 3A			

^{*}Required to meet Pre-Torque specifications



Gauge Tap**

Gaskets

- Used for monitoring pressure/temperature at rupture disk location
- Also available on inlet holder

O-Ring Seal

• Teflon encapsulated Viton

Special Coating

- Fluoropolymer Teflon® Sintered (FS)
 - Provides durable, non-stick surface (Requires O-Ring Seal)

Teflon – TM DuPont HASTELLOY C – TM Haynes International



ZOOK Enterprises, LLC

16809 Park Circle Drive Chagrin Falls, OH 44022 U.S.A.

Toll Free 800.543.1043
Phone 440.543.1010
Fax 440.543.4930
E-mail sales@zook.cc

ZOOK Canada, Inc.

4400 South Service Road Burlington, ON Can. L7L 5R8

Toll Free 800.370.6057 Phone 905.681.2885 Fax 905.681.8838 E-mail sales.canada@zook.cc

ZOOK Europe, LTD.

Navigation House, Bridge Street Killamarsh, Sheffield UK. S21 1AL

Phone **0044 (0) 1909 560999**Fax **0044 (0) 1909 560860**E-mail **zookeurope@zook.cc**